# DOSAPROP PLUS

proportional dosing systems with polyphosphate crystals

Dosing systems designed for the use with drinking water

## DOSAPROP PLUS

#### DOSING SYSTEMS WITH POLYPHOSPHATE CRYSTALS

Proportional dosing system equipped with device providing "Venturi" effect.





## **OSAPROP** PIUS



DOSAPROP PLUS HA



POLYPHOSPHATE CRYSTALS REFILL 0.5 kg and 1.5 kg pack with 6/10 (small) crystals or 10/20 (large) crystals, refill TO DOSAPROP PLUS 3P and DOSAPROP MIGNON PLUS.



Housings are tested and certified under the most stringent procedures worldwide, in compliance with DM 25 (Italy), with the sanitary certification ACS (France), EAC/Ghostreghistrazia (Russia) and WaterMark (Australia).



polyphosphate cartridges HA with antimicrobial flat seal, heights 5", 7", 10", replacements for DOSAPROP HA.



HA MIGNON polyphosphate cartridge with antimicrobial flat seal 5"M refill to DOSAPROP MIGNON HA.

## -U- spanner CODE RB7403013 -L- spanner for Mignon 3P -M- spanner for Mignon 2P CODE RB7403001 CODE RB7403002 -S- wall bracket CODE RB7400007 3/4" brass nipples with o-ring (pair) CODE RB7404001 1" brass nipples with o-ring (pair) CODE RB7404002 3/4" plastic nipple with o-ring CODE LB7404012 lubri it ubri it -LUBRIKIT- single-dose lubricant for housing o-ring CODE RE9020650 SYMBOLS | EGEND For domestic use For technical and industrial use Filter housings made in PET, a highly recyclable plastic, are

ACCESSORIES ON DEMAND



manufactured with a proprietary procedure saving up to 60% of energy in injection molding

compared with standard plastics. That is one of Atlas Filtri commitments to comply with Kyoto Treaty for the reduction of green house gas (CO<sub>2</sub>) emissions in the atmosphere.

HOUSINGS RANGE





ANTI-SCALE SYSTEMS

## 

## $\xrightarrow{B} \xrightarrow{C}$



#### WORKING CONDITIONS

| 8 bar (116 psi)                   |
|-----------------------------------|
| 35°C (95°F)                       |
| 4°C (39,2°F)                      |
| 50°f (500 ppm CaCO <sub>3</sub> ) |
|                                   |

**Remark** - Water treated with polyphosphate can be heated up to a max temperature of 75° - 80°C, beyond that temperature the polyphosphate gradually loses its efficacy.

#### SPECIFICATIONS

Non-toxic materials, suitable for drinking water. Head / ring nut: reinforced polypropylene. Bowl: SAN. O-ring: EPDM. IN/OUT brass threads: CW 617 N brass.

#### DOSAPROP MIGNON PLUS 3P with polyphosphate loose crystals

| HOUSINGS W | ITH BRASS BSP THREADS         |                |     |        |               |    |    |
|------------|-------------------------------|----------------|-----|--------|---------------|----|----|
| CODE       | MODEL                         | APPLICABLE     |     | IN/OUT | DIMENSIONS mm |    |    |
|            |                               | REFILL         | g*  |        | Α             | В  | С  |
| RA401P511  | DOSAPROP MIGNON PLUS L 3P MFO | LOOSE CRYSTALS | 265 | 1/2"   | 176           | 94 | 89 |

g\* = polyposphate crystals amount in grams

#### DOSAPROP MIGNON PLUS 3P with HA polyphosphate crystals cartridge

| HOUSINGS W | ITH BRASS BSP THREADS              |                      |        |      |        |      |
|------------|------------------------------------|----------------------|--------|------|--------|------|
| CODE       | MODEL                              | SUITABLE             | IN/OUT | DIME | NSIONS | 3 mm |
|            |                                    | CARTRIDGE            |        | Α    | В      | С    |
| RA401P514  | DOSAPROP MIGNON PLUS L 3P MFO + HA | HA 5" M SX CARTRIDGE | 1/2"   | 176  | 94     | 89   |

## DOSAPROP MIGNON PLUS 2P

#### DOSAPROP MIGNON PLUS 2P with polyphosphate loose crystals

| HOUSINGS W | ITH BRASS BSP THREADS         |                |     |        |      |        |      |
|------------|-------------------------------|----------------|-----|--------|------|--------|------|
| CODE       | MODEL                         | APPLICABLE     |     | IN/OUT | DIME | NSIONS | 6 mm |
|            |                               | REFILL         | g*  |        | Α    | В      | С    |
| RA401P612  | DOSAPROP MIGNON PLUS L 2P MFO | LOOSE CRYSTALS | 275 | 1/2"   | 176  | 94     | 89   |

g\* = polyposphate crystals amount in grams

#### DOSAPROP MIGNON PLUS 2P with HA polyphosphate crystals cartridge

| HOUSINGS WITH BRASS BSP THREADS |                                    |                      |        |               |    |    |  |
|---------------------------------|------------------------------------|----------------------|--------|---------------|----|----|--|
| CODE                            | MODEL                              | SUITABLE             | IN/OUT | DIMENSIONS mm |    |    |  |
|                                 |                                    | CARTRIDGE            |        | Α             | В  | С  |  |
| RA401P614                       | DOSAPROP MIGNON PLUS L 2P MFO + HA | HA 5" M SX CARTRIDGE | 1/2"   | 176           | 94 | 89 |  |









